



Healkeren<sup>TM</sup>


CE



ULTRA POWERFUL HIFU SYSTEM

**BU:TERA**

## Clinical Picture Aesthetic



## Indications

- Smart mode(Preset mode) at each treatment
- Real Penetration of Depth
- Skin tightening &Lifting
- Short treatment time
- Easy to use small area by pen type handpiece
- Contraction of dermis & SMAS layer by HIFU
- Non Surgical face lifting and tightening
- Face&Body(fat) treatment by one device

From the deep SMAS of skin to the  
dermis and the epidermis

## VARIOUS TREATMENTS AT ONCE!!



- Forehead
- Cheek
- Chin
- Neck
- Abdomen
- Arm



- Deep Wrinkle
- Special area
- Under Eyes
- Nasolabial fold
- Small area

Use freely from small to large area.








Healikeren<sup>TM</sup>

CE

# Smart mode installed for face and body



| Cartridge type    | D1.5     | D3.0     | D4.5     | F10        | F15        |
|-------------------|----------|----------|----------|------------|------------|
| Frequency         | 7MHz     | 7MHz     | 7MHz     | 4MHz       | 4MHz       |
| Depth of the skin | 1.5mm    | 3.0mm    | 4.5mm    | 10mm (Fat) | 15mm (Fat) |
| Pen type          | 1.5mm    | 3.0mm    |          |            |            |
|                   | Standard | Standard | Standard | Optional   | Optional   |

Pen type cartridges For Face:1.5mm,3.0mm

Pen type Handpiece



Standard cartridges For Face:1.0mm,3.0mm,4.5mm  
For Body:10mm,13mm

Standard Handpiece





#### TECHNICAL SPECIFICATIONS

| STANDARD TYPE | FUNCTIONS                               |
|---------------|-----------------------------------------|
| Frequency     | 4MHz, 7MHz                              |
| Max Energy    | 3.0J/cm <sup>2</sup>                    |
| Cartridge     | 7MHz: 1.5mm, 3.0mm, 4.5mm-For Face      |
|               | 4MHz: 10mm, 13mm(option)-For Body & Fat |
| Spacing       | 1.0~2.0mm(0.1mm step)-For Fat           |
| Power Level   | Adjustable 1~10Level                    |
| Length        | Full Length: 25mm, 20mm, 15mm           |
| Spot Size     | <3mm                                    |
| LCD           | 10.2Inchs True Color Touch              |

#### TECHNICAL SPECIFICATIONS

| PEN TYPE    | FUNCTIONS            |
|-------------|----------------------|
| Frequency   | 7MHz                 |
| Max Energy  | 3.0J/cm <sup>2</sup> |
| Cartridge   | 7MHz: 1.5mm, 3.0mm   |
| Power Level | Adjustable 1~10Level |
| Speed       | 1-4shot              |
| Spot Size   | <3mm                 |

#### M/s. Healkeren Medtronics Private Limited

No.4, 2nd Cross, Lakshmipura Main Road, Krishnappa Industrial Estate, Abbigere, Bengaluru - 560 090, Karnataka, India.

Mobile : 93101 18774 / 80882 84888 / 80882 84898, Email : sales@healkeren.com / healkeren@gmail.com / info@healkeren.com

[www.healkeren.com](http://www.healkeren.com)